

SeaOWL UV-A™

SEA OIL-IN-WATER LOCATOR



Sea-Bird Scientific introduces SeaOWL UV-A, a new in-situ oil-in-water sensor. Based upon the highly successful ECO sensor, Sea-Bird Scientific has developed an industry leading oil detection technology with 5X optical resolution improvement over its predecessor.

SeaOWL UV-A measures crude oil-in-water using the same UV-A excitation and blue emission wavelengths (370 nm EX/ 460 nm EM) currently used in the ECO CDOM fluorometer. The SeaOWL UV-A improves the resolution and range of the ECO with a greater depth of field, optimized electronics and dynamic gain stage modulation.

The new dynamic gain provides industry leading sensitivity across a large detection range making saturation unlikely in even the most heavily impacted environments.

The compact SeaOWL UV-A design also includes chlorophyll fluorescence and 700 nm backscattering measurements to discriminate crude oil from phytoplankton and other natural sources of FDOM.



Features

Industry-leading optical resolution.

Wide dynamic gain prevents measurement saturation even within heavily impacted environments.

Three parameters in a single sensor: chlorophyll, backscattering, and Fluorescent Dissolved Organic Matter (FDOM).

Backscattering and chlorophyll fluorescence provide discrimination of crude oil from phytoplankton and other natural sources of FDOM.

Optical Backscattering Wavelength 700 nm Backscattering Sensitivity 700 nm^A 1E-06 m⁻¹ sr⁻¹ Backscattering Range700 nm^A 0-0.04 m⁻¹ sr⁻¹ Chlorophyll EX/EM 470/690 nm Chlorophyll Sensitivity $0.005 \, \mu g/l$ Chlorophyll Range 0.005-250 µg/l FDOM EX/EM 370/460 nm **FDOM Sensitivity** 0.03 ppb QSDE FDOM Range 0.03-900 ppb QSDE Oil Calibration Oil Limit of Detection^B < 80ppb crude oil Oil Sensitivity^c 3 ppb crude oil **Electrical** Digital Output Resolution 14 Bit RS-232 Communication Sample Rate 1 Hz Connector Style MCBH(WB)-6MP Input Voltage 7-15 volts Current, Typical (@7V) 81 mA Mechanical Diameter 56.6 mm (2.23 in) 54.6 mm (2.15 in) Length Weight in Air (approx.) 340 g Displacement 137 ml Pressure Housing Material Titanium 6Al-4V **Environmental** -2 to 38 °C Temperature Range of Calibration^D Storage Temperature Range -20 to 50 °C 2000 m Depth Rating



A) Backscattering specifications are derived from a vicarious calibration with a MCOMS backscattering sensor. Scale factors for backscattering incorporate the target weighting function and the solid angle subtended for the MCOMS optical backscattering sensor. The SeaOWL UV-ATM is highly linear in response to changes in the particle concentration of a specific particle population.

B) The estimated limit of detection (LOD) for the ECO CDOM fluorometer is <300 ppb cruide oil (Conmy et al., 2014), i.e. 30 counts. Using the same count to LOD relationship, LOD for SeaOWL UV-A was derived.

C) Applying the ECO CDOM fluorometer crude oil calibration from Conmy et al., 2014, yields this scale factor.

D) The temperature range through which the instruments are tested for operation. The -2° C minimum covers all natural waters on Earth. Please contact Sea-Bird Scientific for testing to higher temperatures.

